

## Hinweis ZD-Grün (520mW)



Für den **ZD-Grün (520mW)** sollte für eine geeignete Wärmeabfuhr gesorgt werden. Optimalerweise durch die Metallhalterung H2-11M oder ähnlich. Der Spannungsbereich sollte mittig des Lasers sein.

Der Laserwarnaufkleber ist beigelegt. Der Kunde muss dafür sorgen, dass dieser nach der Montage


- an einer geeigneten Stelle angebracht wird.

## Anschlussbelegung:

Kabel mit Texas-Stecker




Variante 1:



- - Spannungsversorgung [schwarz]
- + Spannungsversorgung [rot]

Variante 2:



- - Spannungsversorgung [blau]
- + Spannungsversorgung [rot]
- Schirmung


## Information ZD-Green (520mW)



For the **ZD-Green (520mW)**, a suitable heat dissipation should be ensured. Ideally through the metal bracket H2-11M or similar. The clamping area should be in the middle of the laser.

- The laser warning sticker is enclosed. The customer must ensure that this label is placed after the assembly in a suitable position.
- assembly in a suitable position.


## Wiring:



### Cable with Texas plug




-  - power supply
-  + power supply




### Version 1:



-  - power supply [black]
-  + power supply [red]

### Version 2:



-  - power supply [blue]
-  + power supply [red]
-  protective shielding